

# GRAS 45BB-10

KEMAR with Anthropometric  
Pinna for Ear- and Headphone  
Test, 2-Ch CCP



Connection: Constant Current Power (0  
V/CCP)

Channel(s): 2

ANSI: S3.36, S3.25

IEC: 60318-4

ITU-T Rec. P.57 Type 3.3

based on ITU-T Rec. P.58

---

The 45BB-10 KEMAR is a manikin configured with pre-polarized ear simulators and anthropometric pinnae for dual-channel ear- and headphone test. Its corresponding LEMO equivalent is the [GRAS 45BB-9 KEMAR with Anthropometric Pinna for Ear- and Headphone Test, 2-Ch LEMO](#).

## Introduction

The KEMAR head and torso simulator was introduced by Knowles in 1972 and quickly became the industry standard for hearing-aid manufacturers and research audiologists (visit [KEMAR.us](http://KEMAR.us) to read the full story). It is based on worldwide average human male and female head and torso dimensions. It meets the requirements of ANSI S3.36/ASA58-2012 and IEC 60318-7:2011.

The GRAS 45BB KEMAR has the same dimensions and acoustical properties as the original KEMAR, but has been developed further by GRAS to meet the industry's demand for realistic measurements of hearing aids, headphones and headsets. It provides acoustic diffraction similar to that encountered around the median human head and torso, both in the proximity and in the far field.

As all the preconfigured 45BB KEMARs consist of the same basic 45BB KEMAR Non-configured, plus a set of application specific accessories, the full information about a given KEMAR configuration is obtained by combining the information about the 45BB KEMAR Non-configured and the information for a given configured version as found in the present text. Read about the non-configured KEMAR [here](#).

## Design

The 45BB-10 is a KEMAR head and torso for ear and headphone test, with prepolarized ear simulators and anthropometric pinnae.

It is delivered fully configured, individually calibrated and ready for use. In addition to a system calibration certificate, a USB flash memory with simulation data is included.

The main configuration specific components of the 45BB-10 are the GRAS RA0045-S1 Ear Simulator According to 60318-4 and the KB5000/KB50001

Anthropometric Pinnae:

### *The 60318-4 Ear Simulator*

The acoustic input impedance of the RA0045-S1 Ear Simulator closely resembles that of the human ear and, as a result, loads a sound source in very much the same way.

It complies with IEC 60318-4 and ITU-T P.57. and is measured and calibrated according to ITU-T P.57. It embodies a number of carefully designed volumes connected via well-defined and precisely tuned resistive grooves. In an equivalent electrical circuit, capacitors would represent the volumes, and inductance and resistance would represent respectively air mass and air flow within the resistive grooves.

It is delivered with a built-in [GRAS 40A0](#) 1/2" prepolarized pressure microphone.

Read more about RA0045-S1 [here](#)

### *The Anthropometric Pinna*

Compared to the standardized pinna, the anthropometric pinna embodies a number of improvements to the concha and ear canal, combined with increased collapsability of the helix, and improved mounting. It is made of soft silicone, 35 Shore 00 hardness.

The external shape of the pinna is identical to that of the standardized KEMAR pinna, but concha and ear canal have been modified so that they closely mimic the properties of a real human ear. The ear canal has been extended and is now an integral part of the pinna which seals directly against the ear simulator. Like the human ear, the ear canal has the 1st and 2nd bend, and the interface with the concha is oval. Fit and insertion consistency are much improved over the cylindrically or conically shaped ear canal

extensions that are used with the standard pinna.

The flexibility of the outer ear has been improved, and when mounting supra-aural and circum-aural headphones the pinna now collapses against the head very much like a human ear.

In addition to the traditional push mounting from the outside, the pinna is secured with two screws from the inside of KEMAR's head. These two screws ensure that the pinna is held firmly in place. Therefore, it seals perfectly against the ear simulator and the head, and it is therefore possible to mount and dismount DUTs repeatedly without compromising the seal.

Read more about the Anthropometric Pinnae [here](#).

## Typical Applications

The anatomical shape of the pinna makes it possible to achieve very good fit and sealing with anatomically shaped in-ear transducers.

Controlling the insertion depth is easy, leading to good insertion consistency and highly improved repeatability and accuracy of measurements.

The improved fit and seal also means that the low frequency response is improved. It will allow you to reproduce base notes, as well as effectively measure (active & passive) attenuation.

Therefore, the 45BB-10 KEMAR is ideal for accurate and repeatable testing of headphones, earphones and in-ear hearing protectors.

## Performance and warranty

KEMAR is made of components from our standard portfolio and are all manufactured of high-quality material and branded parts that were chosen and processed to ensure life-long stability and robustness. This, enables us to offer 2 years

warranty against defective materials and workmanship.

Exceptions: Microphones included in KEMAR as for these our normal 5 year warranty apply. The warranty period for cables is 6 months.

Connector type		BNC
Set sensitivity @ 250 Hz ( $\pm 2$ dB)	mV/Pa	12.5
Set sensitivity @ 250 Hz ( $\pm 2$ dB)	dB re 1V/Pa	-38.5
Theoretical dynamic range lower limit with GRAS preamplifier	dB(A)	25
Theoretical dynamic range upper limit with GRAS preamplifier @ +28 V / $\pm 14$ V power supply	dB	151
Theoretical dynamic range upper limit with GRAS CCP preamplifier	dB	146
Resonance frequency	kHz	13.5
Temperature range, operation	$^{\circ}\text{C}$ / $^{\circ}\text{F}$	-30 to 60 / -22 to 140
Temperature range, storage	$^{\circ}\text{C}$ / $^{\circ}\text{F}$	-40 to 65 / -40 to 149
Humidity range non condensing	% RH	0 to 95%
ANSI standard		S3.36, S3.25
IEC standard		60318-4 (former 60711), 60318-7 (former 60959)
ITU-T recommendations		P.380
Weight	g / oz	11.45 k / 404

GRAS Sound & Vibration reserves the right to change specifications and accessories without notice.

## Included items

<a href="#">GRAS 45BB</a>	KEMAR Head & Torso, Non-configured
<a href="#">GRAS KB5000</a>	Large Right Anthropometric Pinna 35 Shore 00
<a href="#">GRAS KB5001</a>	Large Left Anthropometric Pinnar 35 Shore 00
<a href="#">GRAS RA0045-S1</a>	IEC 60318-4 Ear Simulator (Prepol. version, 2 pcs)
GRAS GR1874	Ear Simulator Holder
GRAS GR0408	External Ear Canal
GRAS GR0409	Union Nut
<a href="#">GRAS 26CS</a>	1/4" CCP Short Preamplifier (2 pcs)
<a href="#">GRAS RA0001</a>	Adapter for 1/2" Microphone and 1/4" Preamplifier (2 pcs)
<a href="#">GRAS AA0018-S</a>	Microdot-BNC Cable, 35 cm (2 pcs)
<a href="#">GRAS AA0035</a>	BNC-BNC Cable, 3 m (2 pcs)

## Optional items

### Power Modules for Pre-polarized Ear Simulators and Microphones

<a href="#">GRAS 12AL</a>	1-Channel CCP Power Module with A-weighting filter
<a href="#">GRAS 12AQ</a>	2-Channel Universal Power Module with signal conditioning and PC interface

### For Ear Simulator Calibration

<a href="#">GRAS 42AP</a>	Intelligent Pistonphone (250 Hz or 251.2 Hz, 114 dB +/- 0.05 dB)
<a href="#">GRAS 42AA</a>	Pistonphone (250 Hz, 114 dB +/- 0.08 dB)

### Pinna Simulators

<a href="#">GRAS KB0060</a>	KEMAR Small Right Ear 55 Shore 00
<a href="#">GRAS KB0061</a>	KEMAR Small Left Ear 55 Shore 00
<a href="#">GRAS KB0065</a>	KEMAR Large Right Ear 55 Shore 00

<a href="#">GRAS KB0066</a>	KEMAR Large Left Ear 55 Shore 00
<a href="#">GRAS KB1060</a>	KEMAR Small Right Ear, 35 Shore 00
<a href="#">GRAS KB1061</a>	KEMAR Small Left Ear 35 Shore 00
<a href="#">GRAS KB1065</a>	KEMAR Large Right Ear 35 Shore 00
<a href="#">GRAS KB1066</a>	KEMAR Large Left Ear 35 Shore 00
<a href="#">GRAS KB0090</a>	KEMAR Large Right Ear (VA-Style/SQ) 55 Shore 00
<a href="#">GRAS KB0091</a>	KEMAR Large Left Ear (VA-Style/SQ) 55 Shore 00
<a href="#">GRAS KB1090</a>	KEMAR Large Right Ear (VA-Style) 35 Shore 00
<a href="#">GRAS KB1091</a>	KEMAR Large Left Ear (VA-Style) 35 Shore 00
GRAS KB5000	KEMAR Large Right Anthropometric Pinna 35 Shore 00
<a href="#">GRAS KB5001</a>	KEMAR Large Left Anthropometric Pinna 35 Shore 00

## Ear Mould Simulators

<a href="#">GRAS KB0110</a>	Ear Mould Simulator for 2 mm Inner diameter tubing
<a href="#">GRAS KB0111</a>	Ear Mould Simulator for 3 mm Inner diameter tubing

## Ear Canal Extension and Microphone Holder Kits (kits with 2 pcs and O-rings)

GRAS RA0237	Straight Ear Canal Extension Kit for KEMAR
<a href="#">GRAS RA0238</a>	VA-tapered Ear Canal Extension Kit for KEMAR
GRAS RA0239	Ear canal Extension Kit w. silicone lining for KEMAR
GRAS RA0240	Holder for long 1/2" microphone Kit for KEMAR
GRAS RA0241	Holder for short 1/2" microphone Kit for KEMAR
GRAS RA0243	Holder for 1/2" microphone Kit for KEMAR
GRAS RA0244	O-ring kit for KEMAR, 2 pcs.
GRAS RA0249	Straight Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test
GRAS RA0250	Tapered Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test

## KEMAR Retrofit Kit for Binaural Hearing Aid Test

<a href="#">GRAS RA0251</a>	KEMAR Retrofit Kit for Binaural Hearing Aid Test: The Kit includes Ear Holder Plates, mounting bolts and the RA0249 and RA0250 Ear Canal Extension Kits. Included items are made of POM, Nylon and Teflon.
-----------------------------	---

## Extension Cables

GRAS AA0034	BNC-BNC Cable, 2 m
<a href="#">GRAS AA0035</a>	BNC-BNC Cable, 3 m
GRAS AA0036	BNC-BNC Cable, 5 m
GRAS AA0037	BNC-BNC Cable, 10 m
GRAS AA0039-CL	BNC-BNC Cable, Customized Length, xxxx cm

## Flight Case

GRAS KM0094	PELI Case for KEMAR
-------------	---------------------

## Simulation Model of KEMAR

GRAS KB3000	Simulation Model of KEMAR with large pinnae
GRAS KB3001	Simulation Model of KEMAR with small pinnae

## Stand for KEMAR

GRAS AL0026	Loudspeaker stand for KEMAR, Ø 35 mm
-------------	--------------------------------------

## Miscellaneous

GRAS KB0000	KEMAR Handbook
GRAS KB0010	T-Shirt for KEMAR

GRAS Sound & Vibration reserves the right to change accessories without notice.

# GRAS Worldwide

Subsidiaries and distributors in more  
than 40 countries

GRAS SOUND & VIBRATION A/S  
Skovlytoften 33  
2840 Holte  
Denmark  
Tel: +45 4566 4046  
gras@gras.dk

GRAS SOUND & VIBRATION USA  
2234 East Enterprise Parkway  
Twinsburg, OH 44087  
United States  
Tel: +1 330 425 1201  
sales@gras.us

GRAS SOUND & VIBRATION UK  
Building 115  
Bedford Technology Park Thurleigh,  
MK44 2YA Bedford  
United Kingdom  
Tel: +44 1234 639552  
sales@gras.co.uk

GRAS SOUND & VIBRATION CHINA LTD.  
Rm 1606, Kodak House II  
No. 39 Healthy Street East North Point  
Hong Kong  
China  
Tel: +852 2833 9987  
sales@gras.com.cn



## About GRAS Sound & Vibration

GRAS is a worldwide leader in the sound and vibration industry. We develop and manufacture state-of-the-art measurement microphones to industries where acoustic measuring accuracy and repeatability is of utmost importance in R&D, QA and production. This includes applications and solutions for customers within the fields of aerospace, automotive, audiology, and consumer electronics. GRAS microphones are designed to live up to the high quality, durability and accuracy that our customers have come to expect and trust.

**GRAS** Sound  
& Vibration